

Aufbauanleitung "IsoFrame Wave" Distanzprofil Modul

Mounting instructions

Flying Oval post with distance beams


Item.no:
Midi IS-9426
Maxi IS-9427

Complete with:

- | | | |
|--------------------------------|---------------|---------------|
| 1 Oval post, Base 760 | Midi IS-9426 | Maxi IS-9427 |
| 1 Oval post, Center 750/850 | IS-OP-760-EP | IS-OP-760-EP |
| 1 Oval post, Top 755/855 | IS-OP-750-EP | IS-OP-850-EP |
| 1 Foot | IS-OP-755-TP | IS-OP-855-TP |
| 2 Distance beam, 165 mm | IS-OB-CP | IS-OB-CP |
| 1 Corner trim kit with cut out | IS-CF-82-CTLR | IS-CF-83-CTLR |



Accessories



Literature holder
Item IS-56-LH01

Media screen holder
Item IS-80-T804

iPad holder
Item IS-80-T805

Keyboard plinth
Item IS-CO-8P

Table attachment
Item IS-CO-5T



1 Replace the old corner trims with the new set included in your Flying Oval post module.

2 Attach the two distance beams in the cut outs of the new corner trims.

3 Attach the foot in the base section of oval post lock in place.

4 Start to attach the base section with the distance beams.

5 Mount the center section in top of the base and end with the top post section, locking it into place with the top distance beam.

Item 9514 - 2016.11.14