

Aufbauanleitung "IsoFrame Wave" Distanzprofil Modul

Flying Oval post with distance beams

Item no:
Midi IS-9426
Maxi IS-9427

Complete with:

1 Oval post, Base 760
1 Oval post, Center 750/850
1 Oval post, Top 755/855
1 Foot
2 Distance beam, 165 mm
1 Corner trim kit with cut out

Midi IS-9426
IS-CP-760-BP
IS-CP-750-CP
IS-CP-755-TP
IS-03-CF
IS-165-DP
IS-CF-82-CTLR

Maxi IS-9427
IS-CP-760-BP
IS-CP-850-CP
IS-CP-855-TP
IS-03-CF
IS-165-DP
IS-CF-82-CTLR

Mounting instructions

Accessories

Literature holder
Item IS-02-TH01

Media screen holder
Item IS-80-TB04

iPad holder
Item IS-88-TB05

Keyboard plinth
Item IS-CO-02


Table attachment
Item IS-CO-03



1 Replace the old corner trims with the new set included in your Flying Oval post module.



2 Attach the top distance beam in the cut outs of the new corner trim.



3 Attach the foot in the base section of oval post lock in place.



4 Start to attach the base section with the distance beam.



5 Mount the center section in top of the base and end with the top post section, locking it into place with the top distance beam.